



NOTES:

1. LOGO TO BE SPECIFIED: _____
2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 15,000 LBS. [66,720 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 22,500 LBS. [100,080 N]
3. FURNISHED W/(2) 1/2-13 UNC X 4 1/2 [114] LONG SS PENTA HEAD BOLTS.
4. OLD P/N: C12-3048-03

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

DATE	BY	DATE	WEIGHT	LOGO
04/28/10	JG99	4/28/10	225#	
04/28/10	M69	4/28/10	102kg	
NTS	NTS	NTS		
B	B	B		
DRAWING DESCRIPTION				REV
CDR™ 30 X 48 X 3 COVER				B
STANDARD VERSION				9/10
PROJECT NUMBER				
10880				
SHEET 1 OF 1				
DRAWING NUMBER				
C1B304803A				

