



**NOTES:**

- 1. LOGO TO BE SPECIFIED: \_\_\_\_\_.
- 2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 22,500 LBS. [100,080 N] OVER A 10 [254] X 20 [508] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 33,750 LBS. [150,120 N].
- 3. FURNISHED W/(2) 1/2-13 UNC X 4 1/2 [114] LONG SS CAPTIVE PENTA HEAD BOLTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

DESIGNER PROJECT NUMBER		SHEET 1 OF 1		DRAWING NUMBER	
BY	DATE	WEIGHT	DESCRIPTION	LOGO	REV
333#	6/28/10	333#	QUAZITE	OB	S
151#		151#	STANDARD VERSION		
CHK	DATE	NTS	DRAWING DESCRIPTION		
432#	6/28/10	B	QUAZITE Ø36 X 60 X 3 COVER		
APP	DATE				
416#	6/28/10				