



4X ø7/8 [22] THRU
W/ø1 3/8 [35] X 5/8 [16]
DEEP COUNTERBORE

3/4 [19] X 4 [102] PULL SLOT
W/ø1/4 [6] CENTER PIN
4 PLACES

ø2 [51] THRU HOLE
W/ ø2 5/8 [67] X 1/8 [3]
DEEP C/BORE

NOTES:

1. LOGO TO BE SPECIFIED: _____.
2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 22,500 LBS. [100,080 N] OVER A 10 [254] X 20 [508] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 33,750 LBS. [150,120 N].
3. FURNISHED W/(4) 1/2-13 UNC X 4 1/2 [114] LONG SS CAPTIVE PENTA HEAD BOLTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

DESIGN	BY	DATE	WELDED	355#	161#	 HUBBELL 7001 INDUSTRIAL PARK DR ENDRIDGE CITY, TN 37771 800-348-3082 WWW.HUBBELL.COM	LOGO	0B
CHKD	3/27	6/28/10	NTS	161#	NTS		QUANTITY @ TOLL	S
ENTR			1:2			36 X 72 X 03 COVER	B	
APPR			B			STANDARD VERSION	9/12	
PROJECT NUMBER SP							REVISION NUMBER	
SHEET 1 OF 1							DRAWING NUMBER	C1C367203A