



4X  $\phi 7/8$  [22] THRU  
W/ $\phi 1 3/8$  [35] X  $5/8$  [16]  
DEEP COUNTERBORE

4X  $3/4$  [19] X 2 [51]  
PICK HOLE

**NOTES:**

1. LOGO TO BE SPECIFIED: \_\_\_\_\_.
2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 22,500 LBS. [100,080 N] OVER A 10 [254] X 20 [508] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 33,750 LBS. [150,120 N]
3. FURNISHED W/(4) 1/2-13 UNC X 4 1/2 [114] LONG SS CAPTIVE PENTA HEAD BOLTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.		WEIGHT		LOGO	
BY	DATE	345#	156kg	OB	OB
UHQ	4/11/11	8/28/11		S	S
CHK	3/9/11	8/28/11			
APP	4/6/11	8/28/11			
REV					
DRAWING DESCRIPTION		QUAZITE® 48 X 48 X 3 COVER		REV	
STANDARD VERSION				A	
				9/11	
PROJECT NUMBER		104010		DRAWING NUMBER	
SHEET		1 OF 1		C1C484803A	