



NOTES

1. POLE TESTED AS PER ASTM F711 AND IEC 60855.
2. TOOL TESTED AS PER ASTM F1826 AND IEC 62193.
3. USABLE LENGTHS 12 - 16 ft.
4. RETRACTED LENGTH: 59 in. EXTENDED LENGTH: 16 ft.
5. BASE DIAMETER 1 7/8" TIP DIAMETER 1 1/4".
6. WEIGHT - 5 lb.
7. BUTTON REPAIR KIT: T4031247.
8. STORAGE BAG: P6213.

S.NO.	PART NUMBER	DESCRIPTION	QTY.
1	P4030996P	BASE TUBE 1.87"OD x57.00"	1
2	P4030988P	TUBE 1.47"OD x 52.50"	1
3	P4030989P	TUBE 1.67"OD x 54.75"	1
4	P4031603P	POLE 1.25"OD x 50.30"	1
5	P4031011P	BOTTOM CAP, DIA 1.76"	1
6	P4031815P	PLUG, DIA 1.010"	1
7	P4031005P	PLUG, DIA 1.36"	1
8	P4031004P	PLUG, DIA 1.56"	1
9	P4033002P	BUTTON	2
10	P4033001P	BUTTON	1
11	P4032351P	SPRING, 1.25 LONG	1
12	P4032352P	SPRING 2.00 LONG	2
13	P0010419P	PIN, .187 DIA X .375 LG	8
14	P4031977P	SPRING RETAINER	3
15	P4030467P	THUMBSCREW	1
16	P0010309P	SELF TAPPING SCR, #8-32 STN STL	7
17	M44559	UNIVERSAL DISCONNECT HD	1
18	O66036P	UNIVERSAL POLE HEAD 1-1/4"	1

THIS SYMBOL IDENTIFIES CRITICAL FEATURES

CHANCE®	HUBBELL POWER SYSTEMS, INC.			
	TITLE Telescopic Hotstick			
CONFIDENTIAL THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION, OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	SIZE C	CAT / PART / ASSY NO. C403-1599	DWG NO. TBD	REV -
DO NOT SCALE THIS DRAWING	DRN BY HEM	DATE 20/02/19	SHEET 1 OF 1	