




S.NO	CATALOG NUMBER	L	N
1	RLB500-4SL	8.19 [208]	4
2	RLB500-5SLI	9.38 [238]	5
3	RLB500-6SLI	10.57 [268]	6
4	RLB500-7SLI	11.75 [298]	7
5	RLB500-8SLI	12.95 [329]	8




- CONNECTOR FABRICATED FROM 6061-T6 ALUMINIUM ALLOY FOR CONDUCTIVITY AND STRENGTH.
- CONDUCTOR RANGE: 500 Kcmil - #10 AWG
- SUPPLIED WITH ALUMINIUM RADIAL-TIPPED SET SCREWS.
- INCLUDES INHIBITOR IN ALL PORTS AND STUD-MOUNTING HOLE.
- PATENTED TWO-IN-ONE SHARKBITE™ MOUNTING HOLE FEATURE ALLOWS THE CONNECTOR TO FIT ON A 5/8" - 11 OR 1" - 14 TRANSFORMER STUD. BOTH SIZES FIT IN THE SAME HOLE.
- THE SHARKBITE™ FEATURE ALSO SECURELY LOCKS THE CONNECTOR ONTO THE STUD TO ELIMINATE WOBBLE WHEN INSTALLING THE CONDUCTORS.
- FULLY TESTED TO ANSI C119.4 FOR CLASS 'A' CONNECTORS.
- INSULATED SLIP-FIT WITH PATENTED SHARKBITE™ MOUNT, DUAL RATED CONNECTORS FOR ALUMINIUM OR COPPER CONDUCTORS, STREET LIGHT TAP IS AVAILABLE.

				TO ORDER CMC PRODUCTS		DRAWN BY: TS		NAME OF PART:		CAT. NO.:	
				UNITED STATES 1-513-860-4455		12-29-20		STUD-MOUNT TRANSFORMER CONNECTOR		SEE TABLE	
				CANADA 1-800-361-6975		CHECKED BY:		DWG NO.:		B	
				MEXICO 011-52-722-265-4400				C58701389CI-S (CHARTED)			
				FOR PRODUCT INFO www.cmcclugs.com		DRAWING NOT TO SCALE		SHEET NO: 1 OF 1			
A		NEW DRAWING CREATED		12-29-20		TS					
REV.	DESCRIPTION	ECN	DATE	INIT.							

THIS INFORMATION IS PROPRIETARY TO CONNECTOR MFG. CO. AND IS NOT TO BE DISCLOSED OUTSIDE OF CONNECTOR MFG. CO. WITHOUT A CONFIDENTIALITY AGREEMENT



**CONNECTOR MANUFACTURING CO.**



HAMILTON, OHIO