



ALUMINUM BODY  
SMOOTH JAWS  
BRONZE EYESCREW  
WITH FINE THREADS

MAIN LINE RANGE - MAX. 1.162 DIA.  
MAIN LINE RANGE - MIN. 0.162 DIA.

CAT. NO. C600-1734

FAULT RATING FOR THIS GROUND CLAMP IS  
36,000 AMPS FOR 15 CYCLES AND 25,000 AMPS  
FOR 30 CYCLES PER ASTM F855 SPEC.

LATEST EC NO:		REV.	DATE	CHANGED BY	RESP ENGINEER
EC02158		A	10-31-00	MARTIN	WEST
				DO NOT SCALE THIS DWG	THIRD ANGLE PROJECTION 150 DUAL DIMENSIONS IN=INCH, MM=MILLIMETER
DRN BY:	DATE	TITLE:			SIZE
QUALLS	06-07-98	GROUNDING CLAMP			C
				DWG NO: SA600-1734	

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL A.B. CHANCE COMPANY. NO PUBLICATION, DISTRIBUTION OR REPRODUCTION OF THIS DRAWING OR ITS CONTENTS IS PERMITTED WITHOUT THE WRITTEN CONSENT OF HUBBELL / A. B. CHANCE COMPANY. © 2001 HUBBELL/A.B. CHANCE. UNPUBLISHED - ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS