



TRANSFORMER SPECIFICATIONS	
PRIMARY VOLTAGE(S)	208/277
SECONDARY VOLTAGE(S)	120
RATED V.A.	500
RATED FREQUENCY	50/60
INSULATION CLASS	130°C @ MAX RISE 80°C
AGENCY APPROVALS	UL, CUL
ESTIMATED WEIGHT	19.2 LBS

TERMINAL SCREWS ARE COMBINATION M3.5 X 0.6 PHIL-SLOT WITH SEMS WASHER

DIMENSIONS ARE IN INCHES  
TOLERANCES:  
.XX ± .03  
.XXX ± .010  
ANGULAR: ± 1°

SOURCE N/A  
MATERIAL N/A  
FINISH N/A  
DO NOT SCALE DRAWING

NAME	DATE
DRAWN BY: VS	06/04/20
CHECKED BY:	

PROPRIETARY AND CONFIDENTIAL  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ACME ELECTRIC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ACME ELECTRIC IS PROHIBITED.

DESCRIPTION: 500 VA	
SIZE DWG. NO.	CE500N006
WEIGHT:	LBS. SHEET 1 OF 1