



3/8" DURIUM U-BOLT, (2) 3/8" HEX. DURIUM NUTS, & SPLIT LOCKWASHERS

MATERIAL:
CAST COPPER ALLOY

ACCOMMODATES:
#12 - #2 STR. CU. CABLE 2.06 (.081) - 7.39 (.291) DIA. TO 1 1/4" - 2" PIPE
42.16 (1.660) - 60.33 (2.375) DIA.

NOMINAL BOLT INSTALLATION TORQUE:
20NM (170 IN-LBS) FOR 3/8" DURIUM HARDWARE.

42.16 - 60.33 DIA.
1.660 - 2.375

COPYRIGHT. BURNDY INC. 19 86

THIS DRAWING IS DUAL DIMENSIONED ALL DIMENSIONS IN MILLIMETERS AND INCHES EG. $\frac{25.4 \text{ MM}}{1.00 \text{ INCH}}$ OR 25.4 MM. (1.00 INCH) ORIGINAL DESIGN BASED ON INCH SYSTEM		THIRD ANGLE PROJECTION		REV. DATE REVISION DESCRIPTION BY C'K'D.		GROUND CLAMP		SCALE FULL	
						TYPE G43		DRAWN G.F. 1/27/87 CHECKED	
								DWG. No. CSC29680	

APPROVED BY: ArDm f... 1/27/87