



2X ø1/2 [13] THRU
W/ø1 1/2 [38] X 3/8 [10] DEEP COUNTERBORE

NOTES:

1. LOGO TO BE SPECIFIED: _____
2. FURNISHED W/(2) 3/8-16 S.S. HEX HEAD BOLTS.
3. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 15,000 LBS. [66,720 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 22,500 LBS. [100,080 N].
4. REF: OLD PENCIL NO. DT-2-1118PCLH.



DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.					
		WEIGHT	LOG		
BY	DATE	 Pencil 546 ENGLISH ROAD ROCKY MOUNT, NC 27804 800-257-7448 WWW.PENCIL.COM	LC	DRAWING NUMBER DT1118CLH00	
UAT	9/3		10/18/14		15.9#
CH	9/3		10/27/14		1 1/2" -1"
END					
APP	4/8/14		10/27/14		B
PROJECT NUMBER		SHEET 1 OF 1			