

24X $\phi 1$ [25] THRU HOLE
(12 IN EACH RING)

64 $\frac{3}{4}$
[1645]

34 $\frac{3}{4}$
[883]

INTEGRAL BOTTOM

8
[203]

64 $\frac{3}{4}$
[1645]


1/2-13 UNC
LIFTING BOLT
4 PLACES

34 $\frac{3}{4}$
[883]

NOTES:

1. THIS EXTENSION IS RATED FOR ANSI/SCTE 77 TIER 15 APPLICATIONS.
2. FURNISHED W/(4) 1/2-13 UNC X 8 [203] LONG SS HEX HEAD BOLTS, (8) $\phi 1/2$ SS FLAT WASHERS, AND (4) 1/2-13 UNC SS HEX NUTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

DRN	BY	DATE	WEIGHT	 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com	LOC
CHK	ENG	APR	161# 73kg		LC S
APR	APR	PROJECT NUMBER	SCALE	DRAWING DESCRIPTION QUAZITE® 30 X 60 X 8 EXTENSION W/INTEGRAL BOTTOM STANDARD VERSION	REV
			NTS		A
			SIZE		4/13
			B		
			DRAWING NUMBER		
			EOB306008B		
			SHEET 1 OF 1		