


NOTES:

1. THIS EXTENSION IS RATED FOR ANSI/SCTE 77 TIER 15 APPLICATIONS.
2. FURNISHED W/(4) 1/2-13 UNC X 8 [203] LONG SS HEX HEAD BOLTS, (8) ø1/2 SS FLAT WASHERS, AND (4) 1/2-13 UNC SS HEX NUTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.						
	BY	DATE	WEIGHT	 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com	LOC	
DRN	ALH	4/1/13	161# 73kg		LC	
CHK	JJP	5/2/13	SCALE	DRAWING DESCRIPTION <b>QUAZITE® 30 X 60 X 18 EXTENSION</b> <b>W/INTERGRAL BOTTOM</b> <b>STANDARD VERSION</b>	REV	
ENG			NTS		A	
APR			SIZE			
APR			B			4/13
PROJECT NUMBER				DRAWING NUMBER		
				SHEET 1 OF 1		EOB306018B