


**NOTES:**

1. THIS BOX IS RATED FOR ANSI/SCTE 77 TIER 15 APPLICATIONS.
2. FURNISHED W/(4) 1/2-13 UNC X 8 [203] LONG SS HEX HEAD BOLTS, (8) ø1/2 SS FLAT WASHERS, AND (4) 1/2-13 UNC SS HEX NUTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.					
DRN	BY	DATE	WEIGHT	 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com	LOC
			294# 133kg		LC
CHK			SCALE	DRAWING DESCRIPTION <b>QUAZITE® 36X96X36 EXTENSION            INTEGRAL BOTTOM            STANDARD VERSION</b>	REV
ENG			NTS		<b>A</b>
APR			SIZE		
APR			B		4/13
PROJECT NUMBER				SHEET 1 OF 1	DRAWING NUMBER <b>EOB369636B</b>