

8X ϕ 1 1/4 [32] THRU HOLE
 12 ON BOTTOM RING
 12 ON TOP RING

42 7/8
 [1067]

100 1/4
 [1956]

48
 [1219]

1/2-13 UNC
 LIFTING BOLT
 4 PLACES


BOTTOM OPENING
 36 3/4 [933] X 93 1/4 [1778]

100 1/4
 [1956]

43 1/4
 [1111]

NOTES:

1. THIS BOX IS RATED FOR ANSI/SCTE 77 TIER 15 APPLICATIONS.
2. FURNISHED W/(4) 1/2-13 UNC X 8 [203] LONG SS HEX HEAD BOLTS, (8) ϕ 1/2 SS FLAT WASHERS, AND (4) 1/2-13 UNC SS HEX NUTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.					
DRN	BY	DATE	WEIGHT	 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com	LOC
CHK	ENG	APR	318# 144kg		LC S
APR	APR		SCALE	DRAWING DESCRIPTION QUAZITE® 36X96X48 EXTENSION STANDARD VERSION	REV
			NTS		A
			SIZE		4/13
			B		
PROJECT NUMBER				DRAWING NUMBER	
				EOB369648A	
SHEET 1 OF 1					