


BOTTOM OPENING
 47 1/4 [1236] X
 92 3/4 [2381]

NOTES:

1. THIS EXTENSION IS RATED FOR ANSI/SCTE77 TIER 15 APPLICATIONS.
2. FURNISHED W/(6) 1/2-13 UNC X 5 [203] LONG SS HEX HEAD BOLTS, (12) ø1/2 SS FLAT WASHERS, AND (6) 1/2-13 UNC SS HEX NUTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.						
	BY	DATE	WEIGHT		3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com	LOC
DRN	<i>BFV</i>	4/12/13	317# 144kg			LC
CHK	<i>JJP</i>	5/3/13	SCALE	DRAWING DESCRIPTION QUAZITE® 48 X 96 X 36 EXTENSION	STANDARD VERSION	REV
ENG			NTS			A
APR			SIZE			
APR			B			4/13
PROJECT NUMBER				DRAWING NUMBER		
				SHEET 1 OF 1		EOB489636A