






INSULATION:
1 [25] THICK

LOCKING
STAPLE


SINGLE ANCHOR
PAD (4 PLACES)



CONTINUOUS HINGE
LOCATION

LID PROP
2 PLACES

R3 [76] DRAIN
PORT (1 CENTERED
EACH END)



CUSTOMER APPROVAL

APPROVED BY: _____

DATE: _____

NOTES:

- HEAT IS PROVIDED BY A 90WATT, 120V SINGLE PHASE HEAT TRACE TAPE. FOR UNHEATED VERSION REPLACE THE PREFIX "H" WITH AN "L".
- ENCLOSURE COLOR IS BEIGE.
- FOR RECOMMENDED SLAB SIZE ADD 9" [229] TO THE ENCLOSURE EXTERIOR.

HOTBOX ENCLOSURES ARE NON-RETURNABLE. A SIGNED DRAWING MUST BE RETURNED AT THE TIME OF ORDER. DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.					HUBBELL® 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.hot-box.com		LOC
DRN	BY	DATE	WEIGHT	SCALE	DRAWING DESCRIPTION	HOT BOX® FIBERGLASS FLIP TOP ENCLOSURE HB2	LC
CHK			55.5# 25kg	1 1/2"=1'			S
ENG							REV
APR			SIZE	B			C
APR							8/11
PROJECT NUMBER					DRAWING NUMBER		
09820					HF013039028		
SHEET 1 OF 1							