


LOCKING TELESCOPIC
LID PROP (2 PLACES)

CONTINUOUS
HINGE

R4 3/4 [121]
DRAIN PORT
(1 CENTERED
EACH END)

NOTES:

- HEAT IS PROVIDED BY A 60WATT, 120V SINGLE PHASE HEAT TRACE TAPE. FOR UNHEATED VERSION REPLACE THE PREFIX "H" WITH AN "L".
- STANDARD COLOR IS BEIGE. (OPTIONS AVAILABLE)
- FOR RECOMMENDED SLAB SIZE ADD 9" [229] TO THE ENCLOSURE EXTERIOR.

HOTBOX ENCLOSURES ARE NON-RETURNABLE. A SIGNED DRAWING MUST BE RETURNED AT THE TIME OF ORDER. DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.				 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.hot-box.com		LOC
DRN	BY	DATE	WEIGHT	DRAWING DESCRIPTION	LC	
CHK	ENG	APR	SCALE		REV	
APR	APR	APR	SIZE		B	
PROJECT NUMBER			DRAWING NUMBER		12/10	
09904			HF021033025			
SHEET 1 OF 1						