


ITEM NO.	DESCRIPTION	QTY.
1	LC CONNECTOR DUST CAP	2
2	LC DUPLEX CONNECTOR BODY	1
3	LC CONNECTOR BOOT	2
4	DUPLEX CABLE	A/R
5	SC CONNECTOR BOOT	2
6	SC DUPLEX CLIP	1
7	SC CONNECTOR NUT	2
8	SC CONNECTOR DUST CAP	2

CATALOG NO.	DESCRIPTION	LENGTH	CABLE JACKET COLOR	CONNECTOR HOUSING COLOR
DFPCLSCGEXMM	LC-SC DUPLEX PATCH CORD 50/125um OM3 MULTIMODE	**	AQUA	BEIGE
DFPCLSCDXXMM	LC-SC DUPLEX PATCH CORD 50/125um OM2 MULTIMODE	**	ORANGE	BEIGE
DFPCLSCFXXMM	LC-SC DUPLEX PATCH CORD 50/125um OM4 MULTIMODE	**	AQUA	BEIGE

\*\* AVAILABLE IN 1 METER INCREMENTS UP TO 25 FEET IN LENGTH. REPLACE 'XX' IN THE CATALOG NUMBER WITH APPROPRIATE NUMERICAL LENGTH WHEN ORDERING.



NOTES:

- CONNECTOR OPTICAL, MECHANICAL AND ENVIRONMENTAL PERFORMANCE MEETS TIA568-C.3 SPECIFICATIONS.
- OM3: FIBER IS RATED FOR 10Gb/s TRANSMISSION FOR UP TO 300 METERS AT 850nm.  
OM4: FIBER IS RATED FOR 100Gb/s TRANSMISSION FOR UP TO 150 METERS AT 850nm.
- CONNECTOR USES A PC RADIUS TIP ZIRCONIA CERAMIC FERRULE.
- CONNECTOR HOUSINGS ARE INJECTION MOLDED ENGINEERING PLASTIC RESIN.
- OPTICAL INSERTION LOSS TEST DATA INCLUDED IN EACH BAGGED PATCH CORD.
- CABLE MARKINGS TO IDENTIFY CHANNEL (1 OR 2) AND EACH END (A OR B).
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT PRIOR NOTICE.

DUST CAP SHIPPED INSTALLED

REV.	EGN	DATE	DESCRIPTION	CHG BY	APPD BY
D	18016	9/26/12	ADDED LENGTHS, CHANGED CABLE TYPE	CG	

Created on AUTOCAD		DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1992 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). XX = ±.01 (.25) XXX = ±.005 (.127) XXXX = ±.0025 (.0635) ANGLE TOL. ±1°	
PROJECT REFERENCE:		DRAWN BY: CINDY DUSSAULT 01/18/05 CHECKED BY: APPROVED BY:	
MATERIAL:		TITLE: OM2, OM3 AND OM4 FIBER OPTIC PATCH CORD ASSEMBLY LC-SC DUPLEX 50/125 ENHANCED MULTIMODED	
HUBBELL		Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 141 Lord's Hill Road, Stonington, Connecticut 06378	
SIZE: D	DRAWING NO.: HWS12146C	SCALE: N/A	SHEET 1 OF 1