



ITEM NO.	DESCRIPTION	QTY.	CATALOG NO	DESCRIPTION	FIBER TYPE	CABLE COLOR
1	LC CONNECTOR DUST CAP	4	DFRCLCALCASxxSM	FIBER OPTIC PATCHCORD, RISER, SINGLEMODE, LC/APC-LC/APC DUPLEX, xx* METER	9/125 OS2	YELLOW
2	LC DUPLEX CONNECTOR BODY	2				
3	LC CONNECTOR BOOT	4				
4	DUPLEX CABLE	A/R				

**xx\* MEANS AVAILABLE IN THE FOLLOWING LENGTHS:**  
 1 METER  
 2 METER  
 3 METER  
 4 METER  
 5 METER  
 10 METER



- NOTES:
- CONNECTOR OPTICAL, MECHANICAL AND ENVIRONMENTAL PERFORMANCE MEETS TIA/EIA-568-C.3 SPECIFICATIONS.
  - CONNECTOR USES A APC RADIUS TIP ZIRCONIA CERAMIC FERRULE.
  - CONNECTOR HOUSING IS INJECTION MOLDED ENGINEERING PLASTIC RESIN.
  - OPTICAL INSERTION LOSS AND RETURN LOSS TEST DATA INCLUDED IN EACH BAGGED PATCH CORD.
  - CABLE MARKINGS TO IDENTIFY CHANNEL (1 OR 2) AND EACH END (A OR B).
  - POLARITY: A TO B PER TIA-568.3.
  - SPECIFICATIONS SUBJECT TO CHANGE WITHOUT PRIOR NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
2	21494	09/12/16	UPDATED TABLE	JJRJ	MMA

Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°		PROJECT REFERENCE: 094-13	 <b>Hubbell Premise Wiring</b> HUBBELL INCORPORATED (Delaware) 23 CLARA DRIVE, SUITE 103 MYSTIC, CT 06355	
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL:		TITLE: FIBER PATCH CORDS SINGLEMODE LC/APC-LC/APC DUPLEX 9/125
			DRAWN BY: D.O'CONNOR 12/19/13	SIZE: D	DRAWING NO. HWS14383C
			CHECKED BY:	SCALE: 1/1	REV. 2
		APPROVED BY:	SHEET 1 OF 1		