

CATALOG NO.	CABLE TYPE	PACK QTY.
HCL6CCYY	CATEGORY 6 U/UTP, 4PR, 28 AWG, PATCH	SINGLE
HCL6ACCYY	CATEGORY 6A F/UTP, 4PR, 28 AWG, PATCH	SINGLE
HCL6CCYYX24	CATEGORY 6 U/UTP, 4PR, 28 AWG, PATCH	BULK PACK, 24 CORDS
HCL6ACCYYX24	CATEGORY 6A F/UTP, 4PR, 28 AWG, PATCH	BULK PACK, 24 CORDS


CATALOG NUMBER STRUCTURE

SINGLE PACK: HCL6-CC-YY EXAMPLE: HCL6BK15

24 COUNT BULK PACK: HCL6-CC-YY-X24 EXAMPLE: HCL6BK15X24

CC = CABLE COLOR, SEE TABLE
 YY = LENGTH IN FEET, SEE TABLE
 X24 SUFFIX = 24 COUNT BULK PACK

LENGTH "YY" (ft.)	CABLE COLOR	
	"CC"	COLOR
01	B	BLUE
03	GY	GRAY
05	W	WHITE
07	BK	BLACK
10	P	PURPLE
15	GN	GREEN
20	OR	ORANGE
25	R	RED
30	Y	YELLOW



PIN OUT	
CONTACT #	COLOR
1	OR/W
2	OR
3	GR/W
4	B
5	B/W
6	GR
7	BR/W
8	BR

NOTES:

- CABLE LENGTH TOLERANCE:
 - 1FT. TO 10FT. = +2.00"/-0"
 - >10FT. = +2.00"/-0"
- ROHS COMPLIANT ASSEMBLY.
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
2	22519	10/5/17	ADDED 24 COUNT BULK PACK NOTATION	DPO	MMA
1	21441	5/31/16	INITIAL RELEASE	DMP	

Created on INVENTOR

DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°

IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION


PROJECT REFERENCE:
NPD-00981

MATERIAL:
N/A

DRAWN BY:
D. PECK

CHECKED BY:

APPROVED BY:

 Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 23 CLARA DRIVE, SUITE 103 MYSTIC, CT 06355		TITLE: NEXTSPEED 28AWG PATCH CORDS	
		SIZE C	DRAWING NO. HWS14654C
SCALE: N/A		SHEET 1 OF 1	