




CATALOG NUMBER	DESCRIPTION	WIDTH "W"	PC NO	PART NAME	QTY
ISK4P	4-POST SPACER KIT FOR IS7	3.57	1	KNOB MCMMASTER CARR P/N:57715K23 OR EQUIV.	2
ISK4P7	4-POST SPACER KIT FOR IS7018	5.15	2	ZINC-PLATED STL. FLAT WASHER 3/8" ID, 7/8" OD, .064" MIN THK.	2
ISK4P9	4-POST SPACER KIT FOR IS70920	7.15	3	CARRIAGE BOLT STAINLESS STEEL, 1/4"-20 X 1"	2
			4	UPPER BRACKET - MATERIAL: 18 GAGE C.R.S. BLACK POWDER COAT	2
			5	LOWER BRACKET - MATERIAL: 18 GAGE C.R.S. BLACK POWDER COAT	2
			6	INSTRUCTION SHEET SUPPLIED	1



REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
C	19574	01/13/15	ADDED TWO NEW SIZES	MMA	

<p>NOTES:</p> <ol style="list-style-type: none"> ASSEMBLE COMPONENTS AS SHOWN. SURFACE FINISH: BLACK POWDER COAT SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. 	
--	--

<p>DIMENSIONING AND TOLERANCING PER ANSI Y14.5M-1982. UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [MM]. TOLERANCES .X = ±.03 [.8] .XX = ±.02 [.4] .XXX = ±.0105] ANGLE TOL ±1°</p>		<p>PROJECT REFERENCE:</p>
<p>IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION.</p>		<p>MATERIAL:</p>
<p>Created on AutoCad</p>		<p>DRAWN BY: N.RICHARD 10/08/07</p>
<p>HUBBELL</p>		<p>CHECKED BY:</p>
<p>Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Stonington, Connecticut 06378</p>		<p>APPROVED BY:</p>
<p>TITLE: IFRAME 4-POST SPACER, ASSY</p>		<p>SIZE C</p>
<p>SCALE: 1:2</p>		<p>REV. C</p>
<p>SHEET 1 OF 1</p>		