



CATALOG NUMBER	DESCRIPTION	FIBER TYPE	SPLIT SLEEVE MAT'L	ADAPT. BODY COLOR
OCLC50	OPTICAL CASSETTE LC DUPLEX/MTP	50/125um MULTIMODE	PHOSPHOR BRONZE	BLACK
OCLC62	OPTICAL CASSETTE LC DUPLEX/MTP	62.5/125um MULTIMODE	PHOSPHOR BRONZE	BEIGE
OCLCSM	OPTICAL CASSETTE LC DUPLEX/MTP	9/125um SINGLEMODE	ZIRCONIA	BLUE
OCLC50G	OPTICAL CASSETTE LC DUPLEX/MTP	50/125um OM3	PHOSPHOR BRONZE	AQUA
OCLC50G4	OPTICAL CASSETTE LC DUPLEX/MTP	50/125um OM4	PHOSPHOR BRONZE	AQUA



NOTES
UNLESS OTHERWISE SPECIFIED:

- SUPPLIED WITH PUSH/PULL FASTENERS FOR EASY INSTALLATION/REMOVAL.
- PANELS FIT INTO HUBBELL WALL MOUNT AND RACK MOUNT CABINETS.
- BLACK ELECTROSTATICALLY APPLIED POWDER COAT.
- ADAPTERS SUPPLIED WITH DUST CAPS INSTALLED.
- FULLY TESTED WITH TEST DATA INCLUDED.
- 50/125um ENHANCED MULTIMODE FIBER IS RATED FOR 10Gb/s TRANSMISSION FOR UP TO 300 METERS AT 850nm.
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
E	19601	03/16/15	REVISED MAT. CALLOUT	MMA	

Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .X = ±.03 (.8) .XX = ±.02 (.4) .XXX = ±.010 (.25) ANGLE TOL ±1°		PROJECT REFERENCE:		 Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Stonington, Connecticut 06378
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL: C.R.S. ENGINEERING THERMOPLASTIC		
	DRAWN BY: PAUL S. MAGUIRE 01/09/03		CHECKED BY: JON LUTZEN 01/15/03		TITLE: FIBER OPTICAL CASSETTE LC DUPLEX/MTP
	APPROVED BY: JON LUTZEN 01/15/03		SIZE C	DRAWING NO. 11881C	REV. E
		SCALE: 1/1		SHEET 1 OF 1	