


CATALOG NUMBER	DESCRIPTION	FIBER TYPE	ADAPT. BODY COLOR
OCRJ50	OPTICAL CASSETTE MTRJ/MTP	MULTIMODE 50/125	BLACK
OCRJ62	OPTICAL CASSETTE MTRJ/MTP	MULTIMODE 62/125	BLACK
OCRJ50G	OPTICAL CASSETTE MTRJ/MTP	MM 50/125 L0	AQUA



NOTES  
UNLESS OTHERWISE SPECIFIED:

1. SUPPLIED WITH PUSH/PULL FASTENERS FOR EASY INSTALLATION/REMOVAL.
2. PANELS FIT INTO HUBBELL WALL MOUNT AND RACK MOUNT CABINETS.
3. BLACK ELECTROSTATICALLY APPLIED POWDER COAT.
4. ADAPTERS SUPPLIED WITH DUST CAPS INSTALLED.
5. FULLY TESTED WITH TEST DATA INCLUDED.
6. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
B	16492	10/21/10	ADDED LASER OPTIMIZED CATALOG	CG	

Created on AUTOCAD

DIMENSIONING AND TOLERANCE PER  
ANSI Y14.5M-1982  
UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES (MM).  
TOLERANCES  
.X = ±.03 (.8)  
.XX = ±.02 (.4)  
.XXX = ±.010 (.25)  
ANGLE TOL. ±1°

PROJECT REFERENCE:  
MATERIAL: .060 C.R.S.  
ENGINEERING THERMOPLASTIC

DRAWN BY: PAUL S. MAGUIRE 01/09/03  
CHECKED BY: JON LUITZEN 01/15/03  
APPROVED BY: JON LUITZEN 01/15/03

**HUBBELL**  
Hubbell Premise Wiring  
HUBBELL INCORPORATED (Delaware)  
14 Lord's Hill Road, Stonington, Connecticut 06378

TITLE: FIBER OPTICAL CASSETTE  
MTRJ/MTP

SIZE: DRAWING NO. C 11884C  
SCALE: 1/1 SHEET 1 OF 1