

CATALOG NO.	DESCRIPTION	LABEL COLO
OFCLICK750SC	FIBER,CLEANCLICKER,750CLK,SC,ST FC	BLUE
OFCLICK750LC	FIBER,CLEANCLICKER,750CLK,LC,MU	GREEN

- 750+ cleans & refillable - for lowest cost per clean
- Cleans dust, particulate & oil contamination
- Fast click-to-clean LC, MU, SC, FC, ST, E2000 in & out of adapters
- Part of the industry's most complete line of fiber optic cleaning products
- Easy-to-use on outside plant & premise networks
- Use with Sticklers® Fiber Optic Splice & Connector Cleaner fluid (#MCC-POC03M) for heavily soiled connectors
- Color coded labels & packaging minimize user error & speed cleaning



The Sticklers® CleanClicker™ 1.25mm and 2.5mm fiber optic connector cleaners are the latest cleaning innovation from the experts at Sticklers. These rugged, precision cleaners use a smooth click-to-clean push-action with light tip forces to reduce the risk of end-face damage. With over 750 cleans, the Sticklers CleanClicker is perfect for cleaning any size network, any installation; from single to thousands of connectors. Sticklers CleanClicker cleaners are packaged color-coded by connector size to help users quickly ensure they have the right cleaner for the connector at hand.

Cleans SC, FC, ST, E2000, LC and MU connectors, on jumpers or in adapters, with UPC or APC polishes. Refill cartridges (see photo) also perform 750+ cleanings, with a 30% savings over the cost of a new cleaner.

There's no doubt: Sticklers® CleanClicker™ fiber optic connector cleaners deliver the best cleaning at the lowest cost-per-connector, every time.

Description	Label Color
2.5CleanClicker™ fiber optic connector cleaner 750 cleans; SC, ST, FC, E2000; UPC/APC	■
1.25CleanClicker™ fiber optic connector cleaner 750 cleans; LC, MU; UPC/APC	■

NOTES:

1. KIT SHOULD CONTAIN:

(1) CLEAN CLICKER CONNECTOR CLEANER IN A BOX (9.75 X 1.25 X 1.125)

2. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

<p>Created on INVENTOR</p>				<p>DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES: XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°</p>		<p>PROJECT REFERENCE: NPD-00162</p>		<p>Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 23 CLARA DRIVE, SUITE 103 MYSTIC, CT 06355</p>		
<p>IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION</p>				<p>DRAWN BY: MABBY 08/18/15</p>		<p>TITLE: FIBER OPTIC CONNECTOR CLEANER</p>				
<p>1 21320 09/09/15 INITIAL RELEASE MMA</p>				<p>CHECKED BY:</p>		<p>SIZE: C</p>		<p>DRAWING NO.: HWS14538C</p>		<p>REV.: 1</p>
<p>REV. ECN DATE DESCRIPTION CHG BY APPD BY</p>				<p>APPROVED BY:</p>		<p>SCALE: N/A</p>		<p>SHEET 1 OF 1</p>		