


CATALOG #	COLOR MOLDED BOOT
PS6BKxx	BLACK
PS6Bxx	BLUE
PS6GYxx	GRAY
PS6GNxx	GREEN
PS6ORxx	ORANGE
PS6Pxx	PURPLE
PS6Rxx	RED
PS6Wxx	WHITE
PS6Yxx	YELLOW

ITEM NO.	DESCRIPTION	QTY.
1	C6 SHIELDED STRANDED PATCH CABLE	1
2	PVC STRAIN RELIEF BOOT	2
3	CUSTOM MODULAR PLUG	2
4	TRACEABILITY LABEL 100% TESTED	1

XX - INDICATES LENGTH (SPECIFIED IN FEET)




NOTES

- PATCH CABLE, CATEGORY 6, 26 AWG STRANDED (7/32) TINNED COPPER (REF ITEM NO.1).
- PVC STRAIN RELIEF BOOT (REF ITEM NO.2)
- CONTACTS 50 MICRO INCH GOLD PLATING (REF ITEM NO.3)
- TRACEABILITY LABEL 100% TESTED (REF ITEM NO.4)
- UL LISTED
- SEE WIRING DETAIL FOR WIRING (BOTH ENDS)
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.
- 3FT, 20FT AND 42FT CABLE LENGTH, CAN BE ORDERD WITH GRAY STANDARD PATCH SHIELDED PATCH CORD WITH MOLDED PINK BOOT.

LENGTH (FT)	CARTON QTY
3	200
5	150
7	100
10	90
15	75
20	50
25	35
35	30
50	20
55	18

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
1	22552	1/10/18	INITIAL RELEASE	AK	MMA

Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°		PROJECT: 004-18	 Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Storington, Connecticut 06378
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL: SEE NOTES	
			DRAWN BY: A. Karanxha	TITLE: PS6 SHIELDED SERIES PATCH CORD ASSEMBLIES
			CHECKED BY:	SIZE: C DRAWING NO. HWS14568C REV. 1
		APPROVED BY:	SCALE: N/A SHEET 1 OF 1	