

6

5





4

3

2

1

CATALOG NO.	DESCRIPTION
SP6A	CAT 6A FIELD TERM PLUG
SP6	CAT 6 FIELD TERM PLUG



NOTES:

- PLUGS ACCEPT F/FTP, S/FTP, F/UTP AND UTP SOLID CONDUCTOR CABLE
CONDUCTOR RANGE: 22 TO 26 AWG
CABLE O.D. RANGE: .22" TO .315"
- PLUGS MEET CHANNEL PERFORMANCE REQUIREMENTS SPECIFIED IN TIA-568-C.2
- MATERIALS:
HOUSING: ZINC ALLOY
PLUG CONTACTS: PHOS/BRZ ALLOY WITH 50 MICRO INCHES OF GOLD PLATING
IDC CONTACTS: PHOS/BRZ ALLOY WITH 100 MICRO INCHES OF Tin PLATING
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
3	22612	05/08/18	REVISED CONDUCTOR&CABLE RANGE	AK	MMA
2	22477	6/14/17	REVISED FORMAT	DPO	MMA

Created on AUTOCAD

DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM).
TOLERANCES
.XX = ±.01 (.25)
.XXX = ±.005 (.127)
.XXXX = ±.0025 (.0635)
ANGLE TOL ±1°

IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION

PROJECT REFERENCE: NPD-01486

MATERIAL: SEE NOTE 3

DRAWN BY: D.O'CONNOR 3/23/17

CHECKED BY:

APPROVED BY:



Hubbell Premise Wiring
HUBBELL INCORPORATED (Delaware)
23 CLARA DRIVE, SUITE 103 MYSTIC, CT 06355

TITLE: C6 & C6A FIELD TERM PLUGS

SIZE: **B** DRAWING NO. **HWS14672C** REV. **3**

SCALE: NTS SHEET 1 OF 1