




- NOTES:
1. ALL DIMENSIONS ARE FROM OUTSIDE UNLESS OTHERWISE NOTED (I/S).
 2. ENCLOSURE AND GLAND PLATE FABRICATED FROM 12 GA. CARBON STEEL.
 3. ALL SEAMS ARE CONTINUOUSLY WELDED & GROUND SMOOTH.
 4. DOORS ARE SEALED WITH FOAM-IN-PLACE GASKET.
 5. RIGHT DOOR (MASTER) IS SECURED SHUT WITH A 3-POINT PADLOCKABLE HANDLE WITH BUILT IN DEFEATER.
 6. LEFT DOOR (SLAVE) IS SECURED SHUT WITH A 3-POINT PADLOCKABLE HANDLE WITHOUT DEFEATER.
 7. COLLAR STUDS PROVIDED FOR BACK PANELS (ORDERED SEPARATELY).
 8. FINISH: INTERIOR & EXTERIOR - ANSI-61 GRAY POLYESTER POWDER.
 9. ENCLOSURE IS RATED TYPES 4 & IP66.




LEFT SIDE VIEW




FRONT VIEW





BOTTOM VIEW



TOP VIEW



SECTION B-B
(INSIDE TOP OF ENCL.)



DIMENSIONS ARE IN INCHES (MM). TOLERANCES UNLESS OTHERWISE SPECIFIED ARE AS FOLLOWS:

.X = ± .06 (1.6)
.XX = ± .031 (.8)
.XXX = ± .016 (.25)
Ø = ± .005
ANGLE TOL ± 1°



WIEGMANN
FREEBURG, ILLINOIS, USA

THIS DRAWING IS THE PROPERTY OF WIEGMANN, A DIVISION OF HUBBELL INCORPORATED. IT IS LOANED TO YOU AND MUST NOT BE USED IN ANY WAY DETRIMENTAL TO THE INTEREST OF WIEGMANN. THIS DRAWING IS WIEGMANN'S BEST INTERPRETATION OF THE INFORMATION PROVIDED. ONCE SIGNED/APPROVED BY THE CUSTOMER, WIEGMANN IS NOT LIABLE FOR ERRORS OR CHANGES NOT ACCURATELY REPRESENTED IN THIS DRAWING. WIEGMANN ASSUMES NO LIABILITY OR RESPONSIBILITY FOR EITHER THE DRAWING OR THE PROJECT. THE DRAWING IS PROVIDED SOLELY AS A COURTESY AND CUSTOMER AGREES TO HOLD WIEGMANN HARMLESS FOR ALL DAMAGES IN ANY WAY CONNECTED TO THE DRAWING.

END USER INFORMATION

END USER: ICD

DRAWING NUMBER: -

PART NUMBER: -

DRAWN BY: WF

CHK'D BY: JB

CREATED ON: 4/27/2023

CHK'D DATE: 4/27/2023

PART NUMBER: R7 -R9 Frame Enclosure

DWG. NO. R7 -R9

Frame Enclosure

REV
E

DESCRIPTION:

WRD, N4X/IP66, FS, DD, DISC., C.R.S., 60x78x20

SHEET 1 OF 1