


ITEM NO.	DESCRIPTION	QTY.	CATALOG NO.	FIBER TYPE	FIBER COLOR	MTP CONNECTOR COLOR	LC CONNECTOR COLOR	BOOT COLOR
1	MTP FEMALE CONNECTOR	1	FHPMTLC6SxxF	OS2	YELLOW	GREEN	BLUE	BLUE/WHITE
2	SINGLEMODE AND MULTIMODE FIBER	N/A	FHPMTLCMxxL4F	OM3	AQUA	AQUA	BEIGE	AQUA
3	LC DUPLEX CONNECTOR	6						
4	2.0mm STRAIN RELIEF BOOT	6						
5	2.0mm STRAIN RELIEF BOOT	6						
6	MTP STRAIN RELIEF BOOT	1						


XX = LENGTH IN FEET




NOTES:

- CONNECTOR OPTICAL, MECHANICAL AND ENVIRONMENTAL PERFORMANCE MEETS TIA/EIA-568-C.3 SPECIFICATIONS.
- LC CONNECTORS USE A UPC RADIUS TIP ZIRCONIA CERAMIC FERRULE.
- CONNECTOR HOUSING IS INJECTION MOLDED ENGINEERING PLASTIC RESIN.
- OPTICAL INSERTION LOSS AND RETURN LOSS TEST DATA INCLUDED IN EACH BAGGED PATCH CORD.
- CABLE MARKINGS TO IDENTIFY CHANNEL (1 THRU 6) AND EACH END (A OR B).
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT PRIOR NOTICE.

POS	END A FIBER COLOR
1	BLUE
2	ORANGE
3	GREEN
4	BROWN
5	SLATE
6	WHITE
7	RED
8	BLACK
9	YELLOW
10	VIOLET
11	ROSE
12	AQUA



POS	END B FIBER COLOR
1A	BLUE
1B	ORANGE
2A	GREEN
2B	BROWN
3A	SLATE
3B	WHITE
4A	RED
4B	BLACK
5A	YELLOW
5B	VIOLET
6A	ROSE
6B	AQUA

Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°		PROJECT REFERENCE: 025-12		 Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Stonington, Connecticut 06378		
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL: SEE NOTES				
			DRAWN BY: C. GRIBBLE 4/10/12				
			CHECKED BY:				
APPROVED BY:		TITLE: HYDRA ASSY, MTP FEMALE TO LC DUPLEX OS2/ MM, 12 FIBER, LOOSE TUBE, PLENUM		SIZE C			
3 201123002651 ADDED OM3 VERSION AK MMA		DRAWING NO. HWS14053C		REV. 3			
REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY	SCALE: 1/1	SHEET 1 OF 1