

6

5


4

3

2


1

CATALOG NUMBER	"L" LENGTH	DESCRIPTION
HCUVX20BK	20 FT	USB-C AOC CABLE-VIDEO 20FT LONG



NOTE:

1. PERFORMANCE: 4K 30HZ VIDEO
2. COMPLIES WITH PART 15 CLASS "B" OF THE FCC RULES
3. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTIFICATION.

Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°		PROJECT REFERENCE:		 <b>Hubbell Premise Wiring</b> HUBBELL INCORPORATED (Delaware) 23 CLARA DRIVE, SUITE 103 MYSTIC, CT 06355		
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL:			TITLE: <b>USB TYPE C AOC CABLE 4K VIDEO + USB 2.0 DATA + POWER</b>	
			DRAWN BY: S.RUBAN 08/30/2022		SIZE: <b>C</b>	DRAWING NO.: <b>HWS15043C</b>	REV.: <b>1</b>
			CHECKED BY:		SCALE: <b>N/A</b>		SHEET <b>1</b> OF <b>1</b>
		APPROVED BY:					

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
1	220830023552		INITIAL RELEASE	RSS	MMA