



4		3			2	1		
FIBER TYPE	CABLE COLOR	CONNECTOR TYPE	CONNECTOR COLOR	CABLE OUTER DIAMETER(mm)		ITEM NO.	DESCRIPTION	QUANTITY
NON ARMORED,INDOOR,12F,OS2 SINGLE MODE	YELLOW	LC	BLUE	3.0		1	LC CONNECTOR	12
NON ARMORED,INDOOR,12F,OM4 MULTIMODE	AQUA	LC	BEIGE	3.0		2	FIBER CABLE	1ft -2000 ft
NON ARMORED,INDOOR/OUTDOOR,12F,OS2 SINGLE MODE	BLACK	LC	BLUE	4.8		3	P/N-DATACODE LABEL	1
NON ARMORED,INDOOR/OUTDOOR,12F,OM4 MULTIMODE	BLACK	LC	BEIGE	4.8				

ITEM NO.	DESCRIPTION	QUANTITY
1	LC CONNECTOR	12
2	FIBER CABLE	1ft -2000 ft
3	P/N-DATACODE LABEL	1



NOTES:

- CONNECTOR OPTICAL, MECHANICAL AND ENVIRONMENTAL PERFORMANCE MEETS TIA/EIA-568-C.3 SPECIFICATIONS.
- CONNECTOR HOUSING IS INJECTION MOLDED ENGINEERING PLASTIC RESIN.
- OPTICAL INSERTION LOSS TEST DATA INCLUDED WITH EACH PATCH CORD.
- PULLING EYE SLEEVE IS OPTIONAL.SPECIFY END A OR END B. WHEN USED, CONNECTORS ARE STAGGERED.
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT PRIOR NOTICE.

Created on INVENTOR	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES.XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°	PROJECT REFERENCE:	 <b>HUBBELL®</b> <b>Premise Wiring</b> HUBBELL INCORPORATED (Delaware) 23 CLARA DRIVE, SUITE 103 MYSTIC, CT 06355
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION	MATERIAL:  SEE NOTES	
		DRAWN BY: S.RUBAN 07/14/24	SIZE: C
		CHECKED BY:	DRAWING NO. <b>HWS1533301C</b>
		APPROVED BY:	REV. <b>1</b>
			SCALE: NTS SHEET 1 OF 1

1	240819041831	08/19/24	INITIAL RELEASE	RSS	MMA
REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY