



ENCLOSURE INFORMATION	
P/N:	DESCRIPTION:
23831KBAM	BOX SST 1F 1b, M20 BOTTOM
23804BAB	COVER SST 1F 1b, ONE DEVICE
23203BAAB	ASSY, DIN RAIL HKH 2 TIER
CONTACT BLOCK RATINGS:	
690 VAC, 20A, 50-60 60 VDC, 5A, 110VDC, 1.5A	
1/2 HP @ 120 VAC, 1 HP @ 208/240/277VAC NEMA A600/P600 - PILOT DUTY 350VAC, 20A - TUNGSTEN AC690V 16A AC-12 AC230V 16A AC-15 50-60Hz	
P/N:	DESCRIPTION:
HKH2P5MTV	2 POS SEL SWT MAINTAINED CONTACT, VERT
LEGEND PLATE:	LAM, OFF ON
LOCKOUT DEV.:	N/A
CONTACT 1:	CONTACT BLOCK, FACT SEALED N.O. DRM, 20A
CONTACT 2:	CONTACT BLOCK, FACT SEALED N.C. DRM, 20A

CONTACT BLOCK RATINGS:
690 VAC, 20A, 50-60
60 VDC, 5A, 110VDC, 1.5A
1/2 HP @ 120 VAC, 1 HP @ 208/240/277VAC
NEMA A600/P600 - PILOT DUTY
350VAC, 20A - TUNGSTEN
AC690V 16A AC-12
AC230V 16A AC-15
50-60Hz
TERMINALS RATED FOR 1-2 CONDUCTORS
#22-10 AWG (0.5-4mm²)




TOP VIEW




LEFT SIDE VIEW

FRONT VIEW



SECTION A-A VIEW



BOTTOM VIEW

HKHMOD Series
DATE CODE S/N

CAT. NO.

HKHMOD Series

DATE CODE S/N

Harsh & Hazardous

www.HARSHANDHAZARDOUS.COM

ST. LOUIS, MO 63113

UL
E 0539 I12G Ex de IIC T6...T4 Gb
0539 I12D Ex tb IIIC T85°C...T135°C Db IP66
DEMKO 15 ATEX 1405X
Ex de IIC T6...T4 Gb
Ex tb IIIC T85°C...T135°C Db IP66
IECEx UL 15.0054X
-50°C ≤T≤+60°C
(-40°C ≤T≤+55°C WITH AMMETER)

EX
FOR T-CODES AND FOR ELECTRICAL RATINGS.

Inmetro
ST. LOUIS, MO 63113


INDUSTRIAL CONTROL EQUIPMENT FOR USE IN ZONE CLASSIFIED HAZ. LOCs.
CLASS I, ZONE 1, AEx de IIC T6...T4 Gb; Ex de IIC T6...T4 Gb
CLASS I, AEx tb IIIC T85°C...T135°C Db IP66; Ex tb IIIC T85°C...T135°C Db IP66
CLASS I, DIV.2, GRPs. A,B,C,D; CLASS II, DIV.1, GRPs. E,F,G (CANADA ONLY)
CLASS II, DIV.2, GROUPS E,F,G; CLASS III
CLASS III, TYPE 3/4/4X/12/13; -50°C ≤T≤+60°C

SEE IOM FORM KI466 FOR ELECTRICAL RATINGS.


CERTIFICATION NAME PLATES

DEVICE 1 ASSEMBLY (1F)	
P/N:	DESCRIPTION:
HKH2P5MTV	2 POS SEL SWT MAINTAINED CONTACT, VERT
LEGEND PLATE:	LAM, OFF ON
LOCKOUT DEV.:	N/A
CONTACT 1:	CONTACT BLOCK, FACT SEALED N.O. DRM, 20A
CONTACT 2:	CONTACT BLOCK, FACT SEALED N.C. DRM, 20A

TERMINALS RATED FOR 1-2 CONDUCTORS
#22-10 AWG (0.5-4mm²)




TOP VIEW




LEFT SIDE VIEW

FRONT VIEW



SECTION A-A VIEW



BOTTOM VIEW

HKH SERIES
CONTROL STATION

CAT. NO.

HKH1BSDAS11S

COUNTRY/DATE CODE

WWW.HARSHANDHAZARDOUS.COM

COMMENT:	SGN:	DATE:	ACCEPTANCE:	DRAWN BY:	DATE:	DWG NUMBER:	ITEM:
			CODE 1: APPROVED (NO COMMENTS)			HKH1BSDAS11S	N/A
			CODE 2: APPROVED FOR MANUFACTURING WITH COMMENTS TO BE INCORPORATED	PR	10/26/2016	SALES/QUOTE NO.:	
			CODE 3: NOT APPROVED RE-SUBMIT			N/A	
			CODE 4: FOR INFORMATION ONLY				
REVISION						HKH MODIFIED ENCLOSURE (HKH1BSDAS11S)	