



- NOTES:
1. LOGO TO BE SPECIFIED: \_\_\_\_\_
  2. FINISHED W/ (8) 1/2-13 UNC X 4 [102] LONG S.S. HEX HEAD BOLTS AND (8) 1/2 [13] S.S. FLAT WASHERS.
  3. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 5,000 LBS [22,240 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MINIMUM STATIC TEST LOAD OF 7,500 LBS [33,360 N].
  4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS UNLESS NOTED OTHERWISE.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

REV	BY	DATE	WEIGHT	DESCRIPTION	LOAD
001	802	5/6/98	602#		S
002	899	5/6/98	273kg		S
003	811	5/6/98		3/4"-1"	C
004	899	5/6/98		B	C
005	899	5/6/98			11/04

PROJECT NUMBER: 98301

SHEET 1 OF 1

FRANKLIN TIER 25  
IG4896CA00

HUBBELL  
7501 IND. STR. F-APT. DP  
LENNER CITY, TN 37771  
800-346-3062  
www.quazitte.com

QUAZITTE® COVER