



CHART

HPS NO.	1	2	3	APPLICATION RANGE
	APPLIED LENGTH	LOOP DIAMETER	CONDUCTOR COLOR	
LRO4006AS	20.50	1.77	ORANGE	0.245 TO 0.277 (6.22 TO 7.04 mm)
LRO4012AS	20.50	1.77	RED	0.316 TO 0.357 (8.03 TO 9.07 mm)
LRO4018AS	22.05	1.77	YELLOW	0.358 TO 0.405 (9.09 TO 10.29 mm)
LRO4020AS	23.15	1.77	BLUE	0.406 TO 0.459 (10.31 TO 11.66 mm)
LRO4024AS	29.06	1.77	RED	0.521 TO 0.588 (13.23 TO 14.94 mm)

NOTES:

1. ALUMINUM COVERED STEEL.
2. DIMENSIONS: INCHES (MILLIMETERS).
3. HAND LAY STANDARD DIRECTION: RIGHT.
4. SPOOL INSULATOR SHALL BE PER ANSI 53-1, 53-2 AND 53-3. NECK DIAMETER 1-3/4".

34349	02/04/10	SD	SD	DELMAR	HUBBELL POWER SYSTEMS TITLE SPOOL TIE CUSTOMER DRAWING
EC #	DATE	CHG BY	RESP ENG		
DESC OF DWG: REVISED KEY 1. REMOVED DASHES FROM PART NUMBERS. --- REASON (S) FOR CHANGE: -- DISPOSITION OF MAT'L: --				CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	SIZE DWG NO. CAT / PART / ASSY NO. REV C CC-19102 SEE CHART 01 DO NOT SCALE THIS DRAWING DRN BY SD DATE 09/15/09 SHEET 1 OF 1