



CATALOG NO. HBL25W34
(NOT SHOWN TO SCALE)

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE.
DIMENSIONS ARE IN INCHES [mm].



WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2°	DR. BY AMS	SCALE 1 : 1
	CHK. BY DL	DATE 11/25/24



BUSHINGS



NOTES:

1. DIMENSIONS SHOWN ARE TYPICAL. DIMENSION UNITS: INCHES [mm].
2. DEVICES ARE UL LISTED PER UL 498.
3. DEVICES ARE CSA CERTIFIED PER CSA C22.2 NO.42.
4. DEVICES ARE UL VERIFIED WITH THE CONSTRUCTION & PERFORMANCE REQUIREMENTS OF FEDERAL SPECIFICATION W-C-596H.
5. TWO STRAIN RELIEF BUSHINGS ACCOMMODATE ROUND CORD TYPES S & SJ:
16/3 SJ, 16/3 S, 14/3 S, 12/3 S
6. CERTAIN DEVICES AVAILABLE IN BLACK.
7. THIS PRODUCT HAS BEEN TESTED TO NEMA ENCLOSURE TYPES 3R, 3RX, 4, 4X, 6, 6P, 12 & IEC CLASSIFICATION IP67 WHEN MATED WITH AN EQUIVALENT RATED WATERTIGHT DEVICE. CORD CONNECTORS ARE RATED TYPE 3R, 3RX, 4, 4X AND 12 WHEN SUPPLIED LID IS CLOSED.

WARNING! RISK OF ELECTRIC SHOCK. DO NOT SUBMERGE.
THE ENCLOSURE RATINGS 6, 6P & IP67 OF THIS PRODUCT ARE ONLY INTENDED TO
DEMONSTRATE SUPERIOR RESISTANCE TO WATER INGRESS AND NOT FOR SUBMERSION.