











5



GOTCHA RINGS



 <div style="text-align: center;"> WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT </div>				
TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = $\pm .01$.XXX = $\pm .005$ ANGLE TOL. $\pm 2^\circ$	DR. BY	AMS	SCALE	3/4
	CHK. BY	DL	DATE	11/25/24

CATALOG NO.	HBL26W74	HBL26W75	HBL26W76	HBL26W81	HBL26W82	HBL26W83	HBL26W08
NEMA CONFIG	 L14-20R	 L15-20P	 L16-20P	 L21-20P	 L22-20P	 L23-20P	 NON-NEMA
RATING	20A, 125/250V	20A, 3Ø 250V AC	20A, 3Ø 480V AC	20A, 3Ø Y 120/208V AC	20A, 3Ø Y 277/480V AC	20A, 3Ø Y 347/600V AC	20A, 125/250V
POLES/WIRES	3P/4W GROUNDING	3P/4W GROUNDING	3P/4W GROUNDING	4P/5W GROUNDING	4P/5W GROUNDING	4P/5W GROUNDING	3P/3W NON-GROUNDING

П