



BUSHINGS


M-12627

4


Ø2.77
[Ø70.4]



3.94
[100.0]



CONE SEALS



BROWN

YELLOW

GREY

PINK

GOTCHA RINGS

NOTES:

1. DIMENSIONS SHOWN ARE TYPICAL. DIMENSION UNITS: INCHES [mm].
2. DEVICES ARE UL LISTED PER UL 498.
3. DEVICES ARE CSA CERTIFIED PER CSA C22.2 NO.42.
4. DEVICES ARE UL VERIFIED WITH THE CONSTRUCTION & PERFORMANCE REQUIREMENTS OF FEDERAL SPECIFICATION W-C-596H EXCEPT HBL26W09, HBL28W08, HBL28W09.
5. FIVE STRAIN RELIEF BUSHINGS ACCOMMODATE ROUND CORD TYPES S:








3-WIRE DEVICES: 12/3 S, 10/3 S








4-WIRE DEVICES: 12/4 S, 10/4 S, 8/4 S

5-WIRE DEVICES: 10/5 S, 8/5 S
6. CERTAIN DEVICES AVAILABLE IN BLACK.
7. THIS PRODUCT HAS BEEN TESTED TO NEMA ENCLOSURE TYPES 3R, 3RX, 4, 4X, 6, 6P, 12 & IEC CLASSIFICATION IP67 WHEN MATED WITH AN EQUIVALENT RATED WATERTIGHT DEVICE.

WARNING! RISK OF ELECTRIC SHOCK. DO NOT SUBMERGE.


THE ENCLOSURE RATINGS 6, 6P & IP67 OF THIS PRODUCT ARE ONLY INTENDED TO DEMONSTRATE SUPERIOR RESISTANCE TO WATER INGRESS AND NOT FOR SUBMERSION.

CATALOG NO.	HBL28W47	HBL28W48	HBL28W49	HBL28W74	HBL28W75	HBL28W76	HBL26W09
NEMA CONFIG	 L5-30P	 L6-30P	 L7-30P	 L14-30P	 L15-30P	 L16-30P	 NON-NEMA
RATING	30A, 125V	30A, 250V	30A, 277V AC	30A, 125/250V AC	30A, 3Ø 250V	30A, 3Ø 480V	20A, 120/208V
POLES/WIRES	2P/3W GROUNDING	2P/3W GROUNDING	2P/3W GROUNDING	3P/4W GROUNDING	3P/4W GROUNDING	3P/4W GROUNDING	4P/4W NON-GROUNDING

CATALOG NO.	HBL28W77	HBL28W78	HBL28W81	HBL28W82	HBL28W83	HBL28W08	HBL28W09
NEMA CONFIG	 L17-30P	 L18-30P	 L21-30P	 L22-30P	 L23-30P	 NON-NEMA	 NON-NEMA
RATING	30A, 3Ø 600V AC	30A, 3Ø Y 120/208V AC	30A, 3Ø Y 120/208V AC	30A, 3Ø Y 277/480V AC	30A, 3Ø Y 347/600V AC	30A, 125/250V	30A, 3Ø Y 120/208V
POLES/WIRES	3P/4W GROUNDING	4P/4W GROUNDING	4P/5W GROUNDING	4P/5W GROUNDING	4P/5W GROUNDING	3P/3W NON-GROUNDING	4P/4W NON-GROUNDING

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
PLUGFACE	NYLON	WHITE
TERMINAL COVER	POLYCARB.	CLEAR
BLADES	BRASS	NICKEL
TERMINAL SCREWS	BRASS	NONE/NICKEL/ GREEN
ASSEMBLY SCREWS	SS	
SHELL BODY	TPE	YELLOW/BLACK
SHELL INSERT	NYLON	NATURAL
NUT	PBT	GRAY/BLACK
BUSHINGS	ELASTOMER	BLACK
GOTCHA RING	NYLON	
CONE SEAL	ELASTOMER	BLACK



CATALOG NO. HBL28W47
(NOT SHOWN TO SCALE)

4	REDRAWN IN INVENTOR, REVISED NOTES AND PART IMAGES PER ECN 241209044470 AMS	DL	12/11/24
REV	DESCRIPTION	APP	DATE
THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].			
TITLE WATERTIGHT PLUGS CUSTOMER DRAWING			
 WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT			
TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2°		DR. BY AMS	SCALE 1 / 2
		CHK. BY DL	DATE 11/25/24