






NOTES UNLESS OTHERWISE SPECIFIED:

- 1. DIMENSIONS SHOWN ARE IN INCHES [mm].
- 2. ENCLOSURE TYPE 4X, 12.
- 3. cULus LISTED.
- 4. NSF CERTIFIED AND IP69k RATING.

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
ALL EXTERNAL	UV STABILIZED	
PLASTIC PARTS	POLYESTER/ POLYCARBONATE BLEND	
FRAME	GALVANIZED STEEL	
ALL EXTERNAL SCREWS AND HARDWARE	STAINLESS STEEL	
CONDUIT HUB	ZINC	



CATALOG NO. HBLDS30T
(NOT SHOWN TO SCALE)

2	REVISED CAT NO. PER DCN 240326038044 CAC		04/02/24
1	NEW RELEASE PER DCN 230711031802 CAC		07/24/23
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE.
DIMENSIONS ARE IN INCHES [mm].

CATALOG NO. HBLDS30T	
30 AMP 600V A.C. RATINGS	
HP	VOLTAGE
1 HP	120V AC 1Ø
3 HP	200-240V AC 1Ø
5 HP	480V AC 1Ø
7.5 HP	200-240V AC 3Ø
15 HP	480V AC 3Ø
15 HP	600V AC 3Ø

TITLE			
CIRCUIT-LOCK™ SLOPED DISCONNECT SWITCH			
		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2°		DR. BY CAC	SCALE 1 / 2
		CHK. BY	DATE 07-24-23