





- NOTES UNLESS OTHERWISE SPECIFIED:
- 1. DIMENSIONS SHOWN ARE IN INCHES [mm].
 - 2. ENCLOSURE TYPE 4X, 12.
 - 3. cULus LISTED.
 - 4. NSF CERTIFIED AND IP69k RATING.

CATALOG NO. HBLDS30	
30 AMP 600V A.C. RATINGS	
HP	VOLTAGE
1 HP	120V AC 1∅
3 HP	200-240V AC 1∅
5 HP	480V AC 1∅
7.5 HP	200-240V AC 3∅
15 HP	480V AC 3∅
15 HP	600V AC 3∅

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
ALL EXTERNAL	UV STABILIZED	
PLASTIC PARTS	POLYESTER/ POLYCARBONATE BLEND	
FRAME	GALVANIZED STEEL	
ALL EXTERNAL SCREWS AND HARDWARE	STAINLESS STEEL	
CONDUIT HUB	ZINC	

CATALOG NO. HBLDS30
(NOT SHOWN TO SCALE)

2	REVISED CAT. NO. PER DCN 240326038044 CAC		04/02/24
1	NEW RELEASE PER DCN 230711031802 CAC		07/24/23
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE	
CIRCUIT-LOCK™ SLOPED DISCONNECT SWITCH	
 WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2°	DR. BY CAC CHK. BY SCALE 1 / 2 DATE 07-24-23