


SEE www.hubbellwiringsystems.com/instr
FOR ADDITIONAL DETAIL & INSTRUCTION SHEET


LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	PBT/TPE	
INTERIOR	NYLON	
PINS	CU ALLOY	
TERM. SCREWS	STAINLESS STEEL	PASSIVATE
GLAND CAPS	PBT	
GLAND	RUBBER	
CLAMPS	PBT	
CLAMP NUTS	BRASS	NICKEL
ASSY SCREWS	STAINLESS STEEL	PASSIVATE
BAND CONTACTS	CU ALLOY	SILVER
MAGNET ASSY	STAINLESS STEEL/NYLON/NeFb	



HBLBA4M

HBLBA3M




HBLBA4MN

HBLBA3MN

CONFIGURATION TABLE

CAT. NUMBER	WIRING CONFIGURATION SUPPORTED
HBLBA4M (L-L-L-G)	4W - 3Ø 250VAC 4W - 3Ø 380-415VAC 4W - 3Ø 480VAC
HBLBA3M (L-L-G)	3W - 208VAC 3W - 250VAC 3W - 480VAC
HBLBA4MN (L-L-N-G)	4W - 125/250VAC 4W - 120/208VAC
HBLBA3MN (L-N-G)	3W - 125VAC 3W - 277VAC 3W - 347VAC

1	RELEASED PER DCN 240222037107; WHD DSL	WHD	2/28/24
REV	DESCRIPTION	APP	DATE
THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].			
TITLE BREAKAWAY PLUG			
 WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT			
TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2°	DR. BY WHD	SCALE 1 / 2	
	CHK. BY DSL	DATE 9/10/23	