




**M-13798** | **2**



S1R10PSPZ SHOWN

CATALOG NO.	DIMENSION "A"	RECEPTACLE MARKING
S1R10PSPZ	24.0 IN [609,6]	-
S1R10PSPZ25	25 FT, 762 CM	-
S1R10PSPZC	24.0 IN [609,6]	CONTROLLED
S1R10PSPZ25C	25 FT, 762 CM	CONTROLLED
S1R10PSPZTR	24.0 IN [609,6]	TAMPER RESISTANT

NOTES:

1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS].
2. ALL PLATES SHIPPED WITH (3) MOUNTING SCREWS, NOT SHOWN.
3. S1R10PSPZTR PROVIDED WITH "CONTROLLED" STICKERS.

CAGE CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
COVER PLATE	STEEL	WHITE
RECEPTACLE	THERMOPLASTIC	BLACK
SOLID WIRE	COPPER	SEE DWG.
MOUNTING SCREWS	STEEL	WHITE

DIMENSION SHEET FOR CAT. NO. SEE TABLE

2	NOTE 3 & BASE CATALOG NUMBER ADDED TO THE TABLE PER DCN 220825023421. VM	DJP	09/21/22
1	RELEASED PER DCN23438	AD	11/15/17
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE.

TITLE  
PERIMETER POWER PLATE  
10 INCH FRPT

**HUBBELL** WIRING DEVICE-KELLEMS  
HUBBELL INCORPORATED  
SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2	DR. BY AD	SCALE 1 : 1
	CHK. BY SM	DATE 11/3/17

**B** M-13798 **2**