




M-14514

1



NOTE:  
1. DIMENSIONS ARE IN INCHES [MM] .

TABLE

CATALOG NO.	DESCRIPTION	FLANGE MATERIAL
SB3083WB	FLAT FLANGE, 1-G, RECT, BRS, BEVEL EDGE	BRASS
SA3083WB	FLAT FLANGE, 1-G, RECT, ALU, BEVEL EDGE	ALUMINUM

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
FLANGE	SEE TABLE	BRUSHED
SPACER	POLESTER	GRAY
#6-32 SCREW MTG.	STEEL	ZINC PLATE
GROUND WIRE ASSY	#12 AWG CU	INSULATED
RIVET	BRASS	

1	INITIAL RELEASE PER DCN #220422019408	SW	4/19/22
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE  
1 GANG FLANGE FOR RECTANGULAR FLOOR BOX



TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2'	DR. BY PSV	SCALE 1 : 1
	CHK. BY SW	DATE 4/19/22

DIMENSION SHEET FOR CAT. NO. SEE TABLE

**B**

M-14514

**1**