




M-14516

1



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
FLANGE	SEE TABLE	BRUSHED
SPACER	POLYESTER	GRAY
#6-32 SCREW MTG.	STEEL	ZINC PLATE
GROUNG WIRE ASSY	#12 AWG CU	INSULATED
RIVET	BRASS	

1	INITIAL RELEASE PER DCN #220422019408	SW	4/21/22
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE
3 GANG FLANGE FOR RECTANGULAR FLOORBOX

		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2°	DR. BY PSV	SCALE 1 / 2	
	CHK. BY SW	DATE 4/21/22	

TABLE

CATALOG NO.	DESCRIPTION	FLANGE MATERIAL
SB3085WB	FLAT FLANGE, 3-G, RECT, BRS, BEVEL EDGE	BRASS
SA3085WB	FLAT FLANGE, 3-G, RECT, ALU, BEVEL EDGE	ALUMINUM

NOTE:
1. DIMENSIONS ARE IN INCHES [MM].