



M-14627


1




TYP. 15A DEVICE




TYP. 20A DEVICE



TYP. HOSP. GRADE DEVICE  
(20A DEVICE SHOWN)



SIDE VIEW  
(SAME FOR ALL DEVICES)



BACK VIEW  
(SAME FOR ALL DEVICES)

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
FACE	NYLON 66 (ZYTEL 101F)	-
BASE	NYLON 66 (ZYTEL 101F)	-
BRIDGE	STEEL	GALVANIZED
BRIDGE (HOSP. GRADE ONLY)	BRASS	-
CONTACTS	BRASS	-
MOUNTING SCREWS	STEEL	-
MOUNTING SCREWS (WR ONLY)	STAINLESS STEEL	-
TERMINALS	BRASS	TIN


DIMENSION SHEET FOR CAT. NO.  
SEE TABLE

CONFIGURATION	BROWN	IVORY	WHITE	GRAY	BLACK	RED	LIGHT ALMOND	RATING
15A	GFR15	GFR15I	GFR15W	GFR15GRY	GFR15BLK	GFR15R	GFR15LA	15A/125V
15A TR	GFRTR15	GFRTR15I	GFRTR15W	GFRTR15GRY	GFRTR15BLK	GFRTR15R	GFRTR15LA	15A/125V
15A WR	GFRWR15	GFRWR15I	GFRWR15W	GFRWR15GRY	GFRWR15BLK	GFRWR15R	GFRWR15LA	15A/125V
15A TR-WR	GFRTW15	GFRTW15I	GFRTW15W	GFRTW15GRY	GFRTW15BLK	GFRTW15R	GFRTW15LA	15A/125V
15A HOSP. GRADE	GFR82	GFR82I	GFR82W	GFR82GRY	GFR82BLK	GFR82R	GFR82LA	15A/125V
15A HOSP. GRADE TR-WR	GFRTW82	GFRTW82I	GFRTW82W	GFRTW82GRY	GFRTW82BLK	GFRTW82R	GFRTW82LA	15A/125V
20A	GFR20	GFR20I	GFR20W	GFR20GRY	GFR20BLK	GFR20R	GFR20LA	20A/125V
20A TR	GFRTR20	GFRTR20I	GFRTR20W	GFRTR20GRY	GFRTR20BLK	GFRTR20R	GFRTR20LA	20A/125V
20A WR	GFRWR20	GFRWR20I	GFRWR20W	GFRWR20GRY	GFRWR20BLK	GFRWR20R	GFRWR20LA	20A/125V
20A TR-WR	GFRTW20	GFRTW20I	GFRTW20W	GFRTW20GRY	GFRTW20BLK	GFRTW20R	GFRTW20LA	20A/125V
20A HOSP. GRADE	GFR83	GFR83I	GFR83W	GFR83GRY	GFR83BLK	GFR83R	GFR83LA	20A/125V
20A HOSP. GRADE TR-WR	GFRTW83	GFRTW83I	GFRTW83W	GFRTW83GRY	GFRTW83BLK	GFRTW83R	GFRTW83LA	20A/125V

1	INITIAL RELEASE PER EC 230112026933	MV	01/12/23
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE  
CUSTOMER DWG.  
COMMERCIAL GFCI



TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ±.01 .XXX = ±.005 ANGLE TOL. ±2'	DR. BY MV	SCALE 1 : 1
	CHK. BY KP	DATE 01/12/23