





M-14672 1



DS115STXX
15A SINGLE POLE
- AND -
DS315STXX
15A 3-WAY



DS120STXX
20A SINGLE POLE
- AND -
DS320STXX
20A 3-WAY




NOTES:

1. cULus LISTED - APPROVED IN US & CANADA.
2. MEETS UL20 & UL486E.
3. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSINGS	PC	---
ROCKER	NYLON	---
PLUNGERS	NYLON	---
BRIDGE	STEEL	NICKEL OR ZINC
SCREWS	STEEL	---
TERMINALS	BRONZE	---
CONTACTS	CU/SILVER LAMINATE	POLISHED
SPRING CLAMP	ALLOY	---



ISO VIEW
SCALE 3/4


EDGECONNECT DECORATOR SWITCH 120-277 VAC		
CATALOG NO.	AMP RATING	ROCKER & HOUSING COLOR
DS115STXX	15A	SEE TABLE 1
DS120STXX	20A	SEE TABLE 1
DS315STXX	15A	SEE TABLE 1
DS320STXX	20A	SEE TABLE 1

TABLE 1: COLORS	
-XX	COLOR
-	BROWN
I	IVORY
GY	GRAY
W	WHITE
R	RED
BK	BLACK
LA	LIGHT ALMOND

1	RELEASE TO PRODUCTION PER EC 230412029445 AD	KP	4/19/23
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE
NON-ILLUMINATED 15A/20A EDGE CONNECT DECORATOR SWITCH



TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ±.01 .XXX = ±.005 ANGLE TOL. ±2'	DR. BY AD CHK. BY KP	SCALE 1:1 DATE 4/3/23
---	-------------------------	--------------------------

DIMENSION SHEET FOR CAT. NO. SEE TABLES

B

M-14672

1