




M-14673

1



**DS120STILXX**  
**20A SINGLE POLE**  
**- AND -**  
**DS320STILXX**  
**20A 3-WAY**



**(DS320STIL SHOWN)**


**NOTES:**

1. cULus LISTED - APPROVED IN US & CANADA.
2. MEETS UL20 & UL486E.
3. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].

EDGECONNECT DECORATOR SWITCH 120-277 VAC		
CATALOG NO.	AMP RATING	ROCKER & HOUSING COLOR
DS120STILXX	20A	SEE TABLE 1
DS320STILXX	20A	SEE TABLE 1

TABLE 1: COLORS	
-XX	COLOR
-	BROWN
I	IVORY
GY	GRAY
W	WHITE
R	RED
BK	BLACK
LA	LIGHT ALMOND

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
HOUSINGS	PC	---
ROCKER	NYLON	---
PLUNGERS	NYLON	---
BRIDGE	STEEL	NICKEL OR ZINC
SCREWS	STEEL	---
TERMINALS	BRONZE	---
CONTACTS	CU/SILVER LAMINATE	POLISHED
SPRING CLAMP	ALLOY	---



**ISO VIEW**  
**SCALE 3/4**

1	RELEASE TO PRODUCTION PER EC 230412029445 AD	KP	4/19/23
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE  
**ILLUMINATED 20A EDGE CONNECT DECORATOR SWITCH**



WIRING DEVICE-KELLEMS  
**HUBBELL INCORPORATED**  
 SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ±.01 .XXX = ±.005 ANGLE TOL. ±2'	DR. BY AD CHK. BY KP	SCALE 1 : 1 DATE 4/11/23
---	-------------------------	-----------------------------