



- NOTES:**
- LOGO TO BE SPECIFIED: \_\_\_\_\_
  - FURNISHED W/ (4) 3/8-7 X 2 [51] LG. S.S. HEX HD. BOLTS, 3/8 [10] S.S. FLAT WASHERS AND (4) 3/8 [10] X 1/8 [3] GROMMETS
  - THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 15,000 LBS. [66,720 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MIN. STATIC TEST LOAD OF 22,500 LBS. [100,085 N]
  - DIMENSIONS IN BRACKETS ARE IN MILLIMETERS UNLESS OTHERWISE NOTED.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.		WEIGHT	DATE	REV
BY	DATE	11 #	7/30/00	S
CHKD	7/30/00	5KG		
APP'D	7/29/00	3'-1"		
APP'D		B		D
DRAWING DESCRIPTION		QUAZITE® COVER		
DRAWING NUMBER		9/12		
PROJECT NUMBER		PC0818HG00		
SHEET 1 OF 1				

