



- NOTES:**
1. LOGO TO BE SPECIFIED: _____
 2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 22,500 LBS. [100,085 N] OVER A 10 [254] X 20 [508] AREA AND MUST PASS A MIN. STATIC TEST LOAD OF 33,750 LBS. [150,128 N].
 3. FURNISHED W/ (2) 3/8-7 X 2 1/2 [64] LONG HEX. HEAD AUGER BOLTS, AND (2) 3/8 [10] S.S. WASHERS.
 4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS UNLESS OTHERWISE NOTED.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.		DATE		REV	
BY	DATE	27#	3/7/02	S	3/7/02
CHKD	3/9/02	12K	3/9/02	C	3/9/02
APP'D	3/9/02	B	3/9/02		3/9/02
DRAWING DESCRIPTION		QUAZITTE® COVER		REV	
HUBBELL		HUBBELL		S	
300 - INDUSTRIAL - FARM DR		LENOIR, CT 0, TN 37771		C	
800-349-3062		www.hubbell.com		9/12	
DRAWING NUMBER		02198		PG118HH00	

