



**NOTES:**

1. LOGO TO BE SPECIFIED: \_\_\_\_\_
2. FURNISHED W/ (2) 3/8-7 X 3 1/2 [89] LONG HEX HEAD AUGER BOLTS, (2) 3/8 [10] FLAT WASHERS, AND (2) 3/8 [10] GROMMETS.
3. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 15,000 LBS. [66,720 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MIN. STATIC TEST LOAD OF 22,500 LBS. [100,085 N].
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.

DATE	BY	SCALE	WELDMENT	LOGO
04/11/04	JSP	1/2"=1'	51# 23Kd	S
07/11/04	JSP		Hubbell ® 7021 IND. STRIP PAIR DP -ENGR. CITY, TN 37071 BUC-346-3062 www.hubbell.com	REV
07/13/04	MST		QUAZITE COVER	C
	APP		B	3/12
EPR OR PROJECT NUMBER 04576			SHEET 1 OF 1	DRAWING NUMBER PG1324HG00

