



**NOTES:**

1. LOGO TO BE SPECIFIED: \_\_\_\_\_
2. THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 15,000 LBS. [66,720 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MIN. STATIC TEST LOAD OF 22,500 LBS. [100,085 N].
3. FURNISHED W/(2) 3/8-7 [10] X 2 3/4 [70] LONG HEX HEAD AUGER BOLTS, (2) Ø3/8 [10] WASHERS, & (2) 3/8 [10] GROMMETS.
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.		 HUBBELL® 7021 INDUSTRIAL PARK DR SENIOR CITY, TN 37371 901-366-3042 www.hubbell.com		VOL. 1 <b>100#</b> 45kg	DATE <b>6/18/04</b>	REV <b>S</b>
UOM <b>PCS</b>	QTY <b>1</b>	DATE <b>7/1/04</b>	SCALE <b>1"=1'</b>	DRAWING DESCRIPTION <b>QUAZITTE® COVER</b>		REV <b>E</b>
APPR 	DATE <b>7/13/04</b>	APPR 	SHEET <b>B</b>	PROJECT NUMBER <b>04645</b>		REV <b>3/12</b>
SHEET 1 OF 1			DRAWING NUMBER <b>PG2424HG00</b>			