



SKID RESISTANT SURFACE MS-86

1/2 [13] X 4 [102] PULL SLOT W/ ϕ 1/4 [6] CENTER PIN (2 PLACES)

QUAZITE LOGO

2X ϕ 5/8 [16] THRU HOLE W/ ϕ 1 1/4 [32] X 1/2 [13] DEEP COUNTERBORE

NOTES:

- LOGO TO BE SPECIFIED: ELECTRIC
- FURNISHED W/(2) 3/8-7 X 4 [102] LONG S.S. HEX HEAD AUGER BOLTS & (2) 3/8 [10] S.S FLAT WASHERS.
- THIS COVER IS RATED FOR A STATIC DESIGN LOAD OF 8,000 LBS. [35,584 N] OVER A 10 [254] X 10 [254] AREA AND MUST PASS A MIN. STATIC TEST LOAD OF 12,000 LBS. [53,376 N].



DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.				HUBBELL® 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com		LOC	
DRN	BY	DATE	WEIGHT	SCALE	DRAWING DESCRIPTION	LC	
CHK	MEF	3/16/89	103#			S	
ENG	JJD	3/20/89	47kg			1 1/2"=1'	REV
APR	FMS	3/20/89	SIZE			H	
APR	VJB	3/21/89	B			3/12	
ESR OR PROJECT NUMBER			DRAWING NUMBER				
88259			PG2436CA0017		SHEET 1 OF 1		